






TOLERANCE UNLESS OTHERWISE SPECIFIED:
±.010 (0.25)

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ADD TOLERANCE ±.010 (±0.25)	④
ADD PLATING SPECS R.STA/MONICA MAY/26/2015	
UPDATE SPECS J.TAN NOV.3/2016	⑤



NOTES:

HOUSING: PA66, UL94V-0, COLOR: BLACK

CONTACTS:

PART NO.

MATERIAL & PLATING

A00-108-220-450 0.45MM PHOSPHOR BRONZE

GOLD FLASH PLATING ALL OVER NICKEL


UNDERPLATING

A00-108-620-450 0.35MM COPPER ALLOY

30µIN OF GOLD PLATING ON CONTACT AREA

WITH TIN PLATING ON SOLDER AREA ALL

OVER NICKEL UNDERPLATING



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES
2011/65/EU FOR ROHS COMPLIANCY.

MODULAR JACK TOP ENTRY PCB 8 POSITIONS		ACAD REFERENCE NO. A00-108-220-450	
		DRAWN: R.BLAKEY	DATE: NOV. 13/06
		CHECKED:	DATE:
		PART NUMBER SEE PART NO.	DRAWING NUMBER
EDAC INC TORONTO, ONTARIO CANADA YOUR CONNECTION TO QUALITY & SERVICE		THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC. AND SHALL NOT BE REPRODUCED OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	
A00-108-220-450		ISSUE 5	