

HDMI interface switch, 3 ports

DSW-HDMI-34

- Use one TV with 3 HDMI sources
- No software required
- Perfect digital video and high quality 3D TV and sound



Features

- Switches up to 3 HDMI sources to a single monitor, TV set or plasma screen
- The digital 2.55 GHz bandwidth amplifier increases the transmission distance with about 25 meters and improves the signal quality
- Infrared remote control

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

48
0.06125
4.4
120x25x180 mm
500x350x350 mm
CN
8716309085717
8517620000

Package contents

HDMI Switch
Remote controller
User manual

Specifications

Ports: 3x input, 1x output HDMI port
Interface standard: HDMI + HDCP v.1.4a backward compatible with versions 1.0/1.1/1.2/1.2a/1.3/1.4, compatible with CTS 1.4a, DVI 1.0 standards
Video formats: HDMI of 480i, 576i, 480p, 576p, 720p, 1080i, 1080p, 4K x 2K (3840 x 2160 at 24/25/30 Hz, 4096 x 2160 at 24 Hz)

Input cable distance: up to 15 m AWG26 HDMI standard cable

Output cable distance: up to 25 m AWG26 HDMI standard cable

Power consumption: 5 V DC up to 0.15 A

Dimensions: 77 x 56 x 15 mm

Certificates

