

HDMI splitter, 4 ports

DSP-4PH4-02

PERFECT CONNECTION

- Sends a single HDMI signal to 4 displays
- Signal amplifier Improves signal quality
- Perfect for home theatres, classand conference rooms



Features

- Sends a single HDMI signal to 4 separate monitors, projectors or TV's
- The digital 225 MHz bandwidth amplifier increases the transmission distance with about 10 meters and also improves signal quality
- Supports 3D video

Specifications

Ports: one input receptacle, 4 output HDMI output receptacles, 19 pin (A)
Interface standard: HDMI + HDCP v.1.4 (compatible with all HDMI versions)
Video formats: HDMI (480p/576i/576p/720p/1080i/1080P/4K)
Maximal single-link range: 3840x2160 at 30 Hz
Video amplifier: 0.5...1.0 Vp-p, up to 225 MHz bandwidth, DDC signal 5 Vp-p
Shell material: steel
Power adapter: 5 V DC, 1 A
Dimensions: 146 x 73 x 24 mm

Packaging

Q'ty in crtn, pcs	30
Crtn volume, CUM	0.06075
Crtn weight, kgs	13.65
Individual package size LxWxH:	215x150x60 mm
Carton size LxWxH:	450x300x450 mm
Country of origin	CN
Barcode	8716309085892
Customs code	8517620000

Package contents

Splitter
Power adapter cable
User Manual

