

EN - For pricing and availability in your local country please visit one of the below links:

DE - Informationen zu Preisen und Verfügbarkeit in Ihrem Land erhalten Sie über die unten aufgeführten Links:

FR - Pour connaître les tarifs et la disponibilité dans votre pays, cliquez sur l'un des liens suivants:

[T4582ESD](#)

[T4718ESD 09](#)

[T4718ESD 10](#)

[T4722ESD 0](#)

[T4722ESD 2](#)

[T4723ESD 1](#)

[T4723ESD 2](#)

[T4725ESD 03](#)

[T4741SESD](#)

EN

This Datasheet is presented by
the manufacturer

DE

Dieses Datenblatt wird vom
Hersteller bereitgestellt

FR

Cette fiche technique est
présentée par le fabricant

PRODUCT SPECIFICATION



Brand	C.K
Product Range	Triton ESD Screwdrivers
Catalogue number	4852ESD, 4718ESD, 4722ESD, 4723ESD, 4725ESD, 4730ESD, 4741ESD, 4797ESD
Date	12/11/2008

Range Description A range of screwdrivers with ESD protection
Features • Tri-lobe handles for comfort in use and effective delivery of torque • Electro Statically Dissipative to protect sensitive electronic components • Blades made from premium quality Chrome Vanadium Molybdenum steel for strength • Tips accurately machined for the ultimate screw fit



		 4797		
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T4582ESD	Triton ESD Bit Holder	-	82054000	6
T4718ESD 08	Triton ESD Screwdriver Tamper Proof TX8 x 70mm	-	82054000	6
T4718ESD 0820	Triton ESD Screwdriver Tamper Proof TX8 x 200mm	-	82054000	6
T4718ESD 09	Triton ESD Screwdriver Tamper Proof TX9 x 70mm	-	82054000	6
T4718ESD 10	Triton ESD Screwdriver Tamper Proof TX10 x 80mm	-	82054000	6
T4718ESD 1030	Triton ESD Screwdriver Tamper Proof TX10 x 300mm	-	82054000	6
T4718ESD 15	Triton ESD Screwdriver Tamper Proof TX15 x 80mm	-	82054000	6
T4718ESD 1530	Triton ESD Screwdriver Tamper Proof TX15 x 300mm	-	82054000	6
T4718ESD 20	Triton ESD Screwdriver Tamper Proof TX20 x 90mm	-	82054000	6
T4722ESD 0	Triton ESD Screwdriver PH0 x 60mm	-	82054000	6
T4722ESD 1	Triton ESD Screwdriver PH1 x 80mm	-	82054000	6
T4722ESD 13	Triton ESD Screwdriver PH1 x 300mm	-	82054000	6
T4722ESD 2	Triton ESD Screwdriver PH2 x 100mm	-	82054000	6
T4722ESD 23	Triton ESD Screwdriver PH2 x 300mm	-	82054000	6
T4723ESD 0	Triton ESD Screwdriver PZD0 x 60mm	-	82054000	6
T4723ESD 1	Triton ESD Screwdriver PZD1 x 80mm	-	82054000	6
T4723ESD 2	Triton ESD Screwdriver PZD2 x 100mm	-	82054000	6
T4725ESD 03	Triton ESD Screwdriver Slotted 3 x 75mm	-	82054000	6
T4725ESD 04	Triton ESD Screwdriver Slotted 3 x 100mm	-	82054000	6
T4725ESD 05	Triton ESD Screwdriver Slotted 5 x 125mm	-	82054000	6
T4725ESD 10	Triton ESD Screwdriver Slotted 5 x 250mm	-	82054000	6
T4725ESD 41	Triton ESD Screwdriver Slotted 4 x 100mm	-	82054000	6
T4730ESD	Triton ESD Screwdriver TX Tamperproof Set/5: TX08, TX09, TX10, TX15, TX20	5015969005721	82054000	3
T4741ESD	Triton ESD Screwdrivers Slotted /PZD Set/6: Slotted 3.0x75, 3.0x100, 5.0x135mm. PZD0x60, PZD1x80, PZD2x100	5013969005714	82054000	3
T4741SESD	Triton ESD Screwdrivers Slotted /PH Set/6: Slotted 3.0x75, 3.0x100, 5.0x135mm. PH0x60, PH1x80, PH2x100	5013969005738	82054000	3
T4797ESD	Triton ESD Screwdrivers Long Reach Slotted/PH/TX Set/6: Slotted 5x250, PH1x300, PH2x300, TX08x200, TX10x300, TX15x300	5013969987034	82054000	1

Technical product information	Blade/Shaft Made from chrome molybdenum vanadium steel, hardened to 57-59 HRC, with black non peel finish. Handle The handle core is polypropylene, injection moulded around the blade The handles are shatterproof down to -35°C. and are electrostatically dissipative to DIN EN 61340 5,1 & 5,2
Standards compliance	Slotted screwdrivers DIN 5265, DIN 5263, DIN 5264A PZD/SDV Screwdrivers DIN 5262-B-PZ, DIN 5260-PZ, DIN/ISO 8764-1 & 2 PH Screwdrivers DIN 5262-B-PH, DIN 5260-PH, DIN/ISO 8764-1 & 2
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T4582ESD	32	32	225	95				
T4718ESD 08	26	26	150	29				
T4718ESD 0820	26	26	280	36	-	-	-	-
T4718ESD 09	26	26	150	29	-	-	-	-
T4718ESD 10	29	29	170	40	-	-	-	-
T4718ESD 1030	29	29	390	52	-	-	-	-

T4718ESD 15	29	29	170	42	-	-	-	-
T4718ESD 1530	29	29	390	58	-	-	-	-
T4718ESD 20	29	29	180	46	-	-	-	-
T4722ESD 0	22	22	130	23	-	-	-	-
T4722ESD 1	29	29	170	54	-	-	-	-
T4722ESD 13	29	29	390	85	-	-	-	-
T4722ESD 2	32	32	200	77	-	-	-	-
T4722ESD 23	32	32	400	121	-	-	-	-
T4723ESD 0	23	23	130	22	-	-	-	-
T4723ESD 1	29	29	170	51	-	-	-	-
T4723ESD 2	32	32	200	77	-	-	-	-
T4725ESD 03	23	23	145	21	-	-	-	-
T4725ESD 04	26	26	180	31	-	-	-	-
T4725ESD 05	29	29	215	58	-	-	-	-
T4725ESD 10	29	29	40	77	-	-	-	-
T4725ESD 41	29	29	190	44	-	-	-	-
T4730ESD	-	-	-	-	111	320	35	186
T4741ESD	-	-	-	-	115	320	35	260
T4741SESD	-	-	-	-	115	320	35	264
T4797ESD	-	-	-	-	-	-	-	-

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T4582ESD	110	230	40	651		
T4718ESD 08	80	160	35	221		
T4718ESD 0820	90	283	40	283		
T4718ESD 09	80	160	35	221		
T4718ESD 10	100	173	35	294		
T4718ESD 1030	110	393	40	418		
T4718ESD 15	100	173	35	306		
T4718ESD 1530	110	393	40	454		
T4718ESD 20	100	183	35	330		

T4722ESD 0	60	160	35	177		
T4722ESD 1	100	173	35	378		
T4722ESD 13	110	393	40	616		
T4722ESD 2	110	230	40	543		
T4722ESD 23	110	403	40	832		
T4723ESD 0	60	160	35	171		
T4723ESD 1	100	173	35	360		
T4723ESD 2	110	230	40	543		
T4725ESD 03	60	160	35	165		
T4725ESD 04	100	183	35	240		
T4725ESD 05	110	230	40	429		
T4725ESD 10	110	343	40	568		
T4725ESD 41	100	193	35	318		
T4730ESD	138	322	136	694		
T4741ESD	138	322	136	939		
T4741SESD	138	322	136	951		
T4797ESD	110	403	40	540		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T4582ESD							81	Box
T4718ESD 08							47	Box
T4718ESD 0820							67	Box
T4718ESD 09							47	Box
T4718ESD 10							54	Box
T4718ESD 1030							106	Box
T4718ESD 15							54	Box
T4718ESD 1530							106	Box
T4718ESD 20							54	Box
T4722ESD 0							39	Box
T4722ESD 1							54	Box
T4722ESD 13							106	Box
T4722ESD 2							81	Box
T4722ESD 23							106	Box

T4723ESD 0							39	Box
T4723ESD 1							54	Box
T4723ESD 2							80	Box
T4725ESD 03							38	Box
T4725ESD 04							54	Box
T4725ESD 05							80	Box
T4725ESD 10							105	Box
T4725ESD 41							54	Box
T4730ESD				Box			159	Box
T4741ESD				Box			159	Box
T4741SESD				Box			159	Box
T4797ESD				Box			106	Box

EN - For pricing and availability in your local country please visit one of the below links:

DE - Informationen zu Preisen und Verfügbarkeit in Ihrem Land erhalten Sie über die unten aufgeführten Links:

FR - Pour connaître les tarifs et la disponibilité dans votre pays, cliquez sur l'un des liens suivants:

[T4582ESD](#)

[T4718ESD 09](#)

[T4718ESD 10](#)

[T4722ESD 0](#)

[T4722ESD 2](#)

[T4723ESD 1](#)

[T4723ESD 2](#)

[T4725ESD 03](#)

[T4741SESD](#)

EN

This Datasheet is presented by
the manufacturer

DE

Dieses Datenblatt wird vom
Hersteller bereitgestellt

FR

Cette fiche technique est
présentée par le fabricant