

SKINDICHT® E

SKINDICHT® E, CR incised sealing ring for several clamping ranges, rings can be individually adapted to various cable diameters



Benefits

One seal for several clamping ranges

Rings can be individually adapted to various cable diameters

Application range

Incised sealing ring for SKINDICHT® cable glands

Note

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one packing unit

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001181 ETIM 5.0 Class-Description: Sealing ring
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001181 ETIM 6.0 Class-Description: Sealing ring
Colour delivered:	Black
Material:	CR
Temperature range:	-20 °C to +80 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SKINDICHT® E

Article number	Article designation / size	Outer diameter x bores (mm)	Thickness (mm)	Outer Ø (mm)	Pieces / PU
SKINDICHT® E					
52005780	E 9	13.5 x 5/8	5.5	13.5	250
52003690	E11	16.5 x 7/10/12.5	6.0	16.5	250
52003700	E 13,5	18.5 x 7/10.5/13/16	6.5	18.5	250
52003710	E 16	20.5 x 8/10.5/13.5/16	7.5	20.5	250
52003720	E 21	26.0 x 11/15/18/20	8.0	26.0	100
52003730	E 29	35.0 x 19/23/27/31	9.5	35.0	100
52003740	E 36	45.0 x 25/28/31/35	12.0	45.0	50
52005790	E 42	52.0 x 35.5/39/42.5/46	14.0	52.0	50
52005800	E 48	57.0 x 40.5/44/47/50.5	14.0	57.0	50

Last Update (17.12.2021)

©2021 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16