

1088BM-HS

heavy duty end cutting nippers, bi-material handles H-SAFE



UNI/ISO 5748

with H-SAFE tethered system

	art.	L mm	L1 mm	$\pm$ mm	A mm	S mm	 g
010884036	1088BM-HS	160	9	1,6	28,0	11,0	230
010884040	1088BM-HS	200	11	2,0	36,0	13,0	370

