

55HS
double open end wrenches H-SAFE
UNI-ISO 10102 DIN 3110

with H-SAFE tethered system

		art.	 mm	L mm	A mm	A1 mm	S mm	 g
•		000554012	55HS 6X7	120	15,5	17,5	3,5	21
•		000554021	55HS 8X9	140	19,5	21,5	4,0	34
•		000554030	55HS 10X11	155	23,5	25,5	4,5	47
•		000554042	55HS 12X13	170	27,5	29,5	5,0	69
•		000554054	55HS 14X15	185	31,5	33,5	5,5	92
•		000554060	55HS 16X17	202	35,5	37,5	6,0	122
•		000554066	55HS 18X19	220	39,5	41,5	6,5	134
•		000554075	55HS 20X22	236	43,5	47,5	7,0	207
•		000554078	55HS 21X23	245	45,5	49,5	7,6	245
		000554081	55HS 22X24	245	45,5	49,5	7,6	233
		000554090	55HS 24X27	262	51,5	55,5	8,0	310
•		000554108	55HS 30X32	297	63,5	67,5	9,0	490
		000554117	55HS 34X36	325	68,4	76,1	11,0	614

