


| SYM | DESCRIPTION | APPROVED | DATE |
|-----|-------------|----------|------|
| 1   |             |          |      |
| 2   |             |          |      |
| 3   |             |          |      |
| 4   |             |          |      |



|     |      |             |         | Tolerance (mm)             |             |                    |                      |
|-----|------|-------------|---------|----------------------------|-------------|--------------------|----------------------|
|     |      |             |         | Wire harness size<br>L(mm) | Trunk       | Protection<br>tube | Positioning<br>space |
| 13  |      |             |         | L ≤ 200                    | +20<br>-10  |                    | ±5                   |
| 12  |      |             |         | 200 < L ≤ 500              | +25<br>-10  |                    | ±5                   |
| 11  |      |             |         | 500 < L ≤ 1000             | +40<br>-20  |                    | ±10                  |
| 10  |      |             |         | 1000 < L ≤ 2000            | +60<br>-30  |                    | ±20                  |
| 9   |      |             |         | 2000 < L ≤ 3000            | +80<br>-50  |                    | ±30                  |
| 8   |      |             |         | 3000 < L ≤ 5000            | +100<br>-60 |                    | ±30                  |
| 7   |      |             |         | L > 5000                   | +120<br>-80 |                    | ±40                  |
| 6   |      |             |         |                            |             |                    |                      |
| 5   |      |             |         |                            |             |                    |                      |
| 4   |      |             |         |                            |             |                    |                      |
| 3   |      |             |         |                            |             |                    |                      |
| 2   |      |             |         |                            |             |                    |                      |
| 1   |      |             |         |                            |             |                    |                      |
| SYM | Name | Description | Remarks |                            |             |                    |                      |

|          |              |              |                   |
|----------|--------------|--------------|-------------------|
| APPROVED | Shen Juan    |              |                   |
|          | Li Jie       |              |                   |
| CHECKED  | Zhang Yining | Customer :   | Date : 2021-12-21 |
| UNIT     | mm           | DRAWING NO.  | EXT-SMB90/500     |
| REV      | 1            | CUSTOMER NO. | PAGE: 1/1         |