






APPROVED: _____
 DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	1/19/22	



WASHER



NUT



RECOMMENDED P.C.B LAYOUT

HEX NUT	BRASS	NICKEL
WASHER	BRASS	NICKEL
FIXED MOUNT	ABS	WHITE
INSULATOR	POM	WHITE
FIXED FOOTREST	IRON	NICKEL
LEAD	IRON	GOLD
BODY	ZINC	NICKEL
CENTER CONTACT	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
 Nominal Impedance: 50 ohms
 Frequency range: DC-3G
 Working Voltage: 500V rms @sea level
 Insulator Resistance: 5000 Megohms min.
 Temperature Rating:
 -55°C to +155°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	Ø.X ±.10
.XX ±.020	Ø.XX ±.015
.XXX ±.015	Ø.XXX ±.010

DRAWN	LH	1/19/22
CHECKED	RC	1/19/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH



909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE RIGHT ANGLE BNC FEMALE P.C. BOARD MOUNT		
SIZE X	PART NO. RF1-500-6	REV. -
REF: S00128C	SCALE: NTS	SHEET 1 OF 1