



AGM battery is intended for use in emergency power systems and in other situations where the battery works cyclically.

Performing daily activities you certainly use devices that need current to work efficiently. Some of them draw energy from the network, other devices like electronic toys, quads, UPS or medical equipment need a battery to work. We offer a wide range of solutions to provide them with a stable and safe source of energy. Check out our AGM batteries and choose the variant best suited to your needs.

We design batteries according to the latest AGM technology, which allows them to work longer thanks to the low self-discharge. Feel safe - their advantage is tightness, resistance to high temperatures and various types of shocks. Equipment powered in this way will work without fail for a long time. Qoltec AGM batteries provide up to 10 years of maintenance-free operation.

Wondering where to use our battery? As a permanent energy source or emergency power supply? The answer is: in both situations, it works perfectly. You can treat it like a battery, which is charged and then powers your equipment. In case of a sudden power outage or power surge, you ensure the safety of connected devices.

You get a full guarantee of reliability. You have the possibility of safe battery operation in any position. You want your equipment to work at full capacity without restrictions - now you can be sure that it will receive the needed dose of energy.

You value the quality of purchased equipment so our projects and solutions are focused on meeting your expectations. AGM Batteries are covered by 24 months warranty.

1 / 2

Producer	Qoltec
Rated capacity	12 Ah
Voltage	6 V
Connector	Fast-on 187 (T1)
Service life	10 years (when working with an uninterruptible power supply UPS)
Usage	Alarm systems and monitoring UPS Electronic toys Motorcycles, quads, scooters, etc. Forklifts, golf carts, wheelchairs Solar battery systems Medical equipment Emergency lighting
Dimensions	150 x 50 x 95 mm
Net weight	1.7800 kg
Gross weight	1.8000 kg
Weight deviation	+/- 10%
Warranty	24 months
Float charge	6.75 V - 6.9 V
Cyclic charge	7.2 V - 7.35 V
EAN code	5901878530482