



Qoltec Laser scanner 1D | CCD | USB | White

Product code: 50865

- read 1D codes,
- work at 500 scans per second,
- resistance to falls,
- scanning from different angles.

Reliable and efficient

Barcodes are everywhere. You will find them in warehouses, stores, pharmacies, offices, gyms and many other places that you visit every day. A Qoltec barcode reader is perfect for all of these locations. Our device guarantees:

- reading 1D codes,
- efficient work at the speed of 500 scans per second,
- resistance to falls (from a height of 1.5m),
- scanning codes at different angles, including inverted ones,
- confidence that the code has been read correctly thanks to the sound signaling.

Practical device

The high quality of our barcode scanners is the result of thoughtful design based on the most important aspects of these devices. We know exactly what you expected of them, so to meet the most demanding working conditions we offer:

- CCD screen - ensures durability and resistance to mechanical damage. The reader can also read codes from LCD screens and mobile phones,
- Plug & Play interface - it guarantees the immediate operation of the barcode scanner without installing additional software,
- 1.8m cable length - comfortable to use,
- USB plug - possibility to connect the device to a PC, laptop, the scanner can work 24 hours a day,
- ergonomic shape - easy to hold.

Confidence confirmed by a warranty

You value the quality of purchased equipment so our projects and solutions are focused on meeting your expectations. The Barcode scanner is covered by 24 months warranty.

Technical data

Producer	Qoltec
Package contents	Wired laser barcode scanner USB cable User manual Warranty Card
Scan Type	Single line
Type	Wired
Barcode Types	1D
Usage	Shops Warehouses Offices Libraries Logistic points
Scanning Angel	360 roll slope of 45 deviation of 45
Scanning speed	500 scans / sec.
Supported operating systems	Windows XP/7/8/10 Android Linux MAC
Additional information	Supported languages: English, German, French, Italian, Russian, Finnish, Norwegian
Processor	32 bit
Interface	USB , RS232
Input voltage	5 V
Working current	650 mW (working), 162 mW (stanby), 900mW (maximum)
Source of light	Red LED (aiming)+ White LED (lighting)
Signalling	By sound
Print contrast	30 %
Shock resistance	1.5 m
Working temperature	0°C ~ +50°C
Scanning distance	10 - 600 mm
Color	White with black elements
Material	ABS + PVC + PC
Dimensions	161.5 x 77 x 88 mm
Cable length	1.8 m
Net weight	0,1800 kg
Gross weight	0,3120 kg
Warranty	24 month
Resolution	4 mils
Screen	CCD
Working humidity	20% ~ 85% (no condenstation)
Scan mode	Manual, continous sensing, auto-sensing
Scanning depth	Code 39: 50-80 mm, QR: 40-250 mm
Storage humidity	20% ~ 85% (no condenstation)
EAN code	5901878508658