



PRODUCT-DETAILS

013186

DGF 12.0 SD FLEX HUB

General Information

Global Commercial Alias	013186
Product ID	7B013186
ABB Type Designation	DGF 12.0 SD FLEX HUB
Catalog Description	DGF 12.0 SD FLEX HUB

Additional Information

Coupling Type	Metallic
Coupling Style	Gear
Coupling Size	12
Shaft Spacing	Close Coupled
Coupling Component	Hub
Shaft Attachment	Rough Bore
ATEX Certificate	NO

Sealing and Lubrication

Lubrication	Grease
-------------	--------

Technical

Rated Torque	4412000 in-lb
Maximum Speed	1300 r/min
Horsepower Per 100 Rating	7000 Hp
Angular Misalignment	0.75 °
Parallel Misalignment	0.21 in
Temperature Rating	Maximum 250 °F Minimum -30 °F

Dimensions

Bore Diameter	Maximum 17 in
Bore Length	13.875 in
Outside Diameter	22.75 in
Product Net Width	0 cm

Categories

Mechanical Power Transmission → Couplings → Metallic Couplings → Gear