

FTP Cat6 Patch cord, grey, 1.5 m

PP6-1.5M

- CAT6 AWG26 stranded foil shielded patch cord with moulded strain relief 50u" 8P8C plugs, 1.5m



Specifications

Patch cord category 6 FTP (shielded)
Length: according to the item
Structure: AWG 26 (7 x 0.15 mm wire), CCA
HDPE insulation of the wire: 0.86 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: 7 x 0.12 mm CCA
PVC outer insulation: 6.2 mm
Color: according to the item
Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs	150
Crtn volume, CUM	0.04
Crtn weight, kgs	7.6
Individual package size LxWxH:	150x120x20 mm
Carton size LxWxH:	460x300x290 mm
Country of origin	CN
Barcode	8716309045353
Customs code	8544421000

Certificates

