


FTP Cat6 Patch cord, purple, 5 m

PP6-5M/V



Features

- CAT6 AWG26 stranded foil shielded patch cord with moulded strain relief 50u" 8P8C plugs, 5m
- Snagless boots

Specifications

Patch cord category 6 FTP (shielded)
Length: according to the item
Structure: AWG 26 (7 x 0.15 mm wire), CCA
HDPE insulation of the wire: 0.86 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: 7 x 0.12 mm CCA
PVC outer insulation: 6.2 mm
Color: according to the item
Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

50
0.035
7.4
40x140x140 mm
400x315x280 mm
CN
8716309078078
8544421000

Certificates

