

# FTP Cat6 Patch cord, grey, 7.5 m

## PP6-7.5M

- CAT6 AWG26 stranded foil shielded patch cord with moulded strain relief 50u" 8P8C plugs, 7.5m



### Specifications

Patch cord category 6 FTP (shielded)  
Length: according to the item  
Structure: AWG 26 (7 x 0.15 mm wire), CCA  
HDPE insulation of the wire: 0.86 mm  
With LDPE filler  
With polyester tape  
With aluminum foil  
Drain hose: 7 x 0.12 mm CCA  
PVC outer insulation: 6.2 mm  
Color: according to the item  
Operation up to 250 MHz

### Packaging

|                                |                |
|--------------------------------|----------------|
| Q'ty in crtn, pcs              | 50             |
| Crtn volume, CUM               | 0.052          |
| Crtn weight, kgs               | 10             |
| Individual package size LxWxH: | 50x150x150 mm  |
| Carton size LxWxH:             | 470x330x335 mm |
| Country of origin              | CN             |
| Barcode                        | 8716309045414  |
| Customs code                   | 8544421000     |

### Certificates

