

FTP Cat6 Patch cord, grey, 20 m

PP6-20M

- CAT6 AWG26 stranded foil shielded patch cord with moulded strain relief 50u" 8P8C plugs, 20m



Specifications

Patch cord category 6 FTP (shielded)
Length: according to the item
Structure: AWG 26 (7 x 0.15 mm wire), CCA
HDPE insulation of the wire: 0.86 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: 7 x 0.12 mm CCA
PVC outer insulation: 6.2 mm
Color: according to the item
Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.046
Crtn weight, kgs	10.2
Individual package size LxWxH:	145x95x95 mm
Carton size LxWxH:	380x390x310 mm
Country of origin	CN
Barcode	8716309045445
Customs code	8544421000

Certificates

