

# S/FTP Cat. 6A LSZH patch cord, black, 2 m

PP6A-LSZHCU-BK-2M

- Perfect connection
- Dual shielded for a reliable connection
- Low Smoke Zero Halogen (LSZH) jacket
- Gold plated contacts



## Features

- Patch cord with foil shielded pairs and braided cable, CAT 6A
- Gold plated contacts
- Low Smoke Zero Halogen (LSZH) jacket
- Molded strain reliefs
- Snagless boots

## Packaging

Q'ty in crtn, pcs  
Crtn volume, CUM  
Crtn weight, kgs  
Individual package size LxWxH:  
Carton size LxWxH:  
Country of origin  
Barcode  
Customs code

150  
0.041  
10.43  
130x10x170 mm  
400x300x340 mm  
CN  
8716309098564  
8544421000

## Specifications

Patch cord category 6A SFTP (shielded)  
Length: according to the item  
Structure: AWG 27 (7 x 0.135 mm wire), COPPER  
FM-PE insulation of the wire: 1.0 mm  
With LDPE filler  
With polyester tape  
With aluminum foil  
Drain hose: not used  
With Braid : 16 x 4/0.12mm  
Outer insulation: 5.8 mm  
Color: according to the item  
Operation up to 250 MHz

## Certificates

