

FTP Cat6 Patch cord, white, 15 m

PPB6-15M

- Perfect connection
- Foil shielded for a reliable connection
- Gold plated contacts



Features

- CAT6 stranded FTP shielded patch cord, 8P8C
- Moulded connectors with integrated strain relief
- Snagless boots

Specifications

Patch cord category 6 FTP (shielded)
Length: 15 m
Structure: AWG 26 (7 x 0.15 mm wire), CCA
HDPE insulation of the wire: 0.86 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: 7 x 0.12 mm CCA
PVC outer insulation: 6.2 mm
Color: white
Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs	40
Crtn volume, CUM	0.083
Crtn weight, kgs	16.76
Individual package size LxWxH:	160x160x50 mm
Carton size LxWxH:	615x365x370 mm
Country of origin	CN
Barcode	8716309121132
Customs code	8544421000

Certificates

