

S/FTP Cat. 8 LSZH patch cord, black, 2 m

PP8-LSZHCU-BK-2M

- Perfect connection
- Dual shielded for a reliable connection
- Low Smoke Zero Halogen (LSZH) jacket
- Gold plated connectors and contacts



Features

- Patch cord with foil shielded pairs and braided cable, CAT 8
- Gold plated connectors and contacts
- Low Smoke Zero Halogen (LSZH) jacket
- Molded strain reliefs
- Snagless boots

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

100
0.037
7.66
175x125x10 mm
405x305x300 mm
CN
8716309120647
8544421000

Specifications

Patch cord category 8 SSTP (shielded)
Length: according to the item
Structure: AWG 27 (7 x 0.135 mm wire), COPPER
FM-PE insulation of the wire: 1.0 mm
With LDPE filler
With polyester tape
With aluminum foil
Drain hose: not used
With Braid : 16 x 5/0.12mm
Outer insulation: 5.8 mm
Color: according to the item
Operation up to 2000 MHz

Certificates

