


UTP Cat6 Patch cord, 0.25 m, yellow

PP6U-0.25M/Y



Features

- CAT6 stranded unshielded (UTP) patch cord, 8P8C
- Snagless boots

Specifications

Patch cord category 6 UTP (unshielded)
Length: according to the item
Structure: AWG 26 (7 x 0.15 mm wire), CCA
HDPE insulation of the wire: 0.85 mm
With LDPE filler
With polyester tape: not used
With aluminum foil: not used
Drain hose: not used
PVC outer insulation: 6.2 mm
Color: according to the item
Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs	500
Crtn volume, CUM	0.04
Crtn weight, kgs	10.15
Individual package size LxWxH:	170x130x15 mm
Carton size LxWxH:	400x300x330 mm
Country of origin	CN
Barcode	8716309093033
Customs code	8544421000

