

UTP Cat6 Patch cord, 5 m, blue

PP6U-5M/B

- Perfect connection
- Gold plated contacts



Features

- CAT6 stranded unshielded (UTP) patch cord, 8P8C
- Snagless boots

Specifications

Patch cord category 6 UTP (unshielded)
Length: according to the item
Structure: AWG 26 (7 x 0.15 mm wire), CCA
HDPE insulation of the wire: 0.85 mm
With LDPE filler
With polyester tape: not used
With aluminum foil: not used
Drain hose: not used
PVC outer insulation: 6.2 mm
Color: according to the item
Operation up to 250 MHz

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

50
0.036
6.34
200x150x30 mm
400x300x300 mm
CN
8716309093156
8544421000

Certificates

