


CLIFF

SEE FCR7350SA1
FOR COLOUR VARIANT




—FCR7350SA2

—FCR7350SA3

PCB STAND OFF






FMF -

PCB LAYOUT
COMPONENT SIDE

RATED
1kV CAT III - 24A
Operating temp -40°C to +80°C

VARIANTS

PART NO.	COLOUR
FCR7350B	BLACK
FCR7350R	RED
FCR7350G	GREEN
FCR7350L	BLUE
FCR7350N	BROWN
FCR7350Y	YELLOW



ISS.	AMEND	DATE
1	1st DRAWN	29/08/06
2	BORDER+RATINGS	03/09/10
3	STAND OFF DIMS ADD	13/12/11
4	SUPPORT PIN ADD	30/04/13
5	PIN TOL., LEGS 4.4mm	28/02/14
6	Ø6.20 WAS Ø6.40	13/06/18
7	ADD BROWN VARIANT	20/01/22

RoHS
✓ COMPLIANT

TOLERANCE
NO DEC. PLACE ± 0.50
1 DEC. PLACE ± 0.20
2 DEC. PLACE ± 0.10
HOLE $\varnothing \pm 0.10$
ANGLES $\pm 1/2^\circ$
UNLESS
OTHERWISE STATED

DO NOT SCALE

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK

Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.

3rd ANGLE PROJECTION:

MATERIAL: NYLON 6 (UL-94 V2) / BRASS

FINISH:	AS MOULDED / GOLD PLATED
---------	--------------------------

DRAWN: T.J.O.

APPROVED: D.P.J.

TITLE: S16N-PC 4mm PANEL SOCKET

DRWG. No. **FCR7350**

FORM: A4DRWGH

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED
TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2006