



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288160874 | <b>Size:</b>                  | 50x7x6 mm |
| <b>Part number:</b>    | 05204126001   | <b>Weight:</b>                | 8 g       |
| <b>Article number:</b> | 867/4 IPR     | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For recessed TORX PLUS® IPR screws with safety pin
- Ductile and tough for hard materials
- TORX PLUS® IPR bit with bore hole on the output side
- 1/4" hexagon drive (Wera connecting series 4)
- Suitable for AEG, ARO, Atlas-Copco, Biax, Black & Decker, Bosch, Buckeye Tools etc.

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

**Web link**

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_tamper-proof\\_torx\\_plus\\_ipr\\_screws\\_with\\_safety\\_pin\\_867\\_4\\_ipr.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_4_ipr.html)

Wera - 867/4 IPR  
05204126001 - 4013288160874

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Bits for Tamper-proof TORX PLUS® IPR Screws with Safety Pin

For recessed TORX PLUS® IPR screws with safety pin

Tough-absorbing bits



A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.



Tough-absorbing Wera bits (Z) prevent any premature breakage of the drive tip.

## Further versions in this product family:

|                    |  | <br>mm | <br>inch | <br>mm |
|--------------------|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| 05160821001        | 10 IPR                                                                             | 50                                                                                       | 2                                                                                            | 4.0                                                                                        |
| 05134657001        | 10 IPR                                                                             | 89                                                                                       | 3 1/2                                                                                        | 4.0                                                                                        |
| 05134654001        | 15 IPR                                                                             | 50                                                                                       | 2                                                                                            | 4.0                                                                                        |
| 05134720001        | 15 IPR                                                                             | 89                                                                                       | 3 1/2                                                                                        | 4.0                                                                                        |
| <b>05204126001</b> | <b>20 IPR</b>                                                                      | <b>50</b>                                                                                | <b>2</b>                                                                                     | <b>4.5</b>                                                                                 |
| 05259135001        | 20 IPR                                                                             | 89                                                                                       | 3 1/2                                                                                        | 4.5                                                                                        |
| 05134655001        | 25 IPR                                                                             | 50                                                                                       | 2                                                                                            | 6.0                                                                                        |
| 05134722001        | 25 IPR                                                                             | 89                                                                                       | 3 1/2                                                                                        | 6.0                                                                                        |
| 05134656001        | 27 IPR                                                                             | 50                                                                                       | 2                                                                                            | 6.0                                                                                        |
| 05134658001        | 27 IPR                                                                             | 89                                                                                       | 3 1/2                                                                                        | 6.0                                                                                        |
| 05134732001        | 30 IPR                                                                             | 50                                                                                       | 2                                                                                            | 6.0                                                                                        |
| 05134723001        | 30 IPR                                                                             | 89                                                                                       | 3 1/2                                                                                        | 6.0                                                                                        |

## Web link

[https://products.wera.de/en/bits\\_holders\\_adaptors\\_the\\_range\\_of\\_bits\\_bits\\_for\\_tamper-proof\\_torx\\_plus\\_ipr\\_screws\\_with\\_safety\\_pin\\_867\\_4\\_ipr.html](https://products.wera.de/en/bits_holders_adaptors_the_range_of_bits_bits_for_tamper-proof_torx_plus_ipr_screws_with_safety_pin_867_4_ipr.html)

Wera - 867/4 IPR  
05204126001 - 4013288160874

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)