

Type ANM

Automotive Blade Fuse

Miniature



www.optifuse.com

(619) 593-5050



Specifications:

- Voltage: 32VDC
- Amperage: 2A, 3A, 4A, 5A, 7.5A, 10A, 15A, 20A, 25A, 30A
- Body: PA 66
- Terminals: Zinc alloy
- Designed to meet SAE and ISO 8820 Standards.
- Interrupt Rating – 1000A @ 32 VDC

Part Number	Amperage	Body Color
ANM-2A	2A	Gray
ANM-3A	3A	Violet
ANM-4A	4A	Pink
ANM-5A	5A	Tan
ANM-7.5A	7.5A	Brown
ANM-10A	10A	Red
ANM-15A	15A	Blue
ANM-20A	20A	Yellow
ANM-25A	25A	Clear
ANM-30A	30A	Green

Time Characteristics:		
% of Rated Current	Min Hold Time	Max Hold Time
110%	100h	~
135%	~	1800s
200%	~	5s

Mechanical Dimensions: Inches [mm]



Warning:



-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.

-Avoid contact of device with chemical solvent. Prolonged contact will damage the device performance.

Note: All specifications subject to change without notice.

Rev C 06/2018 - Page: 1/1
Code H02-01H