

MPMP ARCA 3030

FIBOX
Enclosing innovations



Sample image

Order symbol: MPMP ARCA 3030

Product nbr: 8120921

Description: Mounting plate
multiperforated (250x250x2 mm -
ø3.6 mm)

Remarks: Galvanized steel. for size
300x300x210

Including:

EAN: 6418074089489

El. number:

- Finland: 3424535
- Denmark:
- Sweden:

Dimensions:	Length	Width	Height
-------------	--------	-------	--------

mm:		250	250
-----	--	-----	-----

inch:		9.84	9.84
-------	--	------	------

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation:	Not insulated
------------------------	---------------

Halogen free (DIN/VDE 0472, Part 815):	0
--	---

UV resistance:	-
----------------	---

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

Certificates:
