

MPX ARCA 5050

FIBOX
Enclosing innovations



Sample image

Order symbol: MPX ARCA 5050

Product nbr: 8120740

Description: Mounting plate
(450x450 mm)

Remarks: Isolated. for sizes
500x500x210

Including:

EAN: 6418074314710

El. number:

- Finland: 3424443
- Denmark:
- Sweden:

Dimensions:	Length	Width	Height
-------------	--------	-------	--------

mm:		450	450
-----	--	-----	-----

inch:			
-------	--	--	--

Materials:

Material:

Base colour:

Cover colour:

Gasket material:

Temperatures:

Temperature °C (short term):

Temperature °C (continuous):

Temperature °F (short term):

Temperature °F (continuous):

Rating:

Ingress protection (EN 60529):

Impact Resistance (EN 62262):

Electrical insulation: Not insulated

Halogen free (DIN/VDE 0472, Part 815): 0

UV resistance: -

Flammability Rating:

Glow Wire Test (IEC 695-2-1) °C:

NEMA Class

Certificates: