

# HG 2420 E

Case

EAN 4007841 008284

Article number 008284



CE



VDE

## Function description

Reliability for all demands. Electronically controlled HG 2420 E hot air tool. 2200 W, infinitely variable temperature setting from 80 – 650 °C in 9 steps by thumbwheel. Airflow regulation in 2 stages from 150l/min to 400l/min. Suitable for construction site use, integrated fine dust filter. Outlet nozzle suitable for screw-on Professional nozzles.

## Technical specifications

|                                  |                                   |
|----------------------------------|-----------------------------------|
| Output                           | 2200 W                            |
| Temperature                      | 80 – 650 °C                       |
| Airflow rate                     | 150 – 400 l/min                   |
| Motor, type                      | Brush motor                       |
| Function, life expectancy, motor | 1000 h                            |
| Temperature setting              | 9-stage                           |
| Temperature display              | Thumbwheel with labelled settings |
| Heating element                  | Ceramic heating element           |
| Loc function                     | No                                |
| Residual heat indicator          | No                                |
| Function, hanger                 | No                                |

|                             |                          |
|-----------------------------|--------------------------|
| Replaceable heating element | No                       |
| Restart protection          | No                       |
| Thermal cut-out             | Yes                      |
| Thermostat                  | No                       |
| Cord length                 | 3 m                      |
| Dimensions (L x W x H)      | 337 x 75 x 89 mm         |
| Mains power supply          | 220 – 230 V / 50 – 60 Hz |
| PU1, net weight             | 0,96 kg                  |
| Manufacturer's Warranty     | 1 year                   |
| PU1, EAN                    | 4007841008284            |

# HG 2420 E

Case

EAN 4007841 008284

Article number 008284



## Accessories

|                     |                                                   |
|---------------------|---------------------------------------------------|
| EAN 4007841 071219  | HDPE plastic welding rod                          |
| EAN 4007841 093211  | Pressure roller 50mm - Rubber                     |
| EAN 4007841 009106  | Fast welding nozzle 3mm narrow - for 5mm rd. noz. |
| EAN 4007841 009090  | Flat nozzle 60x2 mm for bitumen                   |
| EAN 4007841 011925  | Flat angled nozzle 30x2 mm, 60°                   |
| EAN 4007841 010423  | Tarpaulin shears                                  |
| EAN 4007841 058821  | Pro Cut cutting system                            |
| EAN 4007841 093013  | Stamped steel plate weld slide                    |
| EAN 4007841 011833  | Fillet weld feeder                                |
| EAN 4007841 011765  | Fast welding nozzle 4mm narrow - for 5mm rd. noz. |
| EAN 4007841 092214  | Round nozzle 5 mm                                 |
| EAN 4007841 009076  | Round nozzle extended 5 mm                        |
| EAN 4007841 010287  | Fast welding nozzle 5mm - for 5mm rd. noz.        |
| EAN 4007841 013240  | Flat angled nozzle 20x2 mm - straight             |
| EAN 4007841 073114  | PVC plastic welding rod                           |
| EAN 4007841 011888  | Shell reflector nozzle 150 x 25 mm                |
| EAN 4007841 010409  | Sieve reflector nozzle 50 x 35 mm                 |
| EAN 4007841 092917  | Quarter-moon crucible steel knife                 |
| EAN 4007841 010263  | Fast welding nozzle 3mm - for 5mm rd. noz.        |
| EAN 4007841 010270  | Fast welding nozzle 4mm - for 5mm rd. noz.        |
| EAN 4007841 034566  | HL Tool Stand                                     |
| EAN 4007841 011840  | Fast welding nozzle 5mm narrow - for 5mm rd. noz. |
| EAN 4007841 092016  | Flat angled nozzle 40x2 mm                        |
| EAN 4007841 011857  | Reflector nozzle 20mm                             |
| EAN 4007841 006785  | Pressure roller 40mm - Silicone                   |
| EAN 4007841 092313  | Round nozzle 10 mm                                |
| EAN 4007841 009083  | Flat nozzle 40x2 mm perforated                    |
| EAN 4007841 074210  | ABS plastic welding rod                           |
| EAN 4007841 011871  | Soldering reflector nozzle                        |
| EAN 4007841 092115  | Flat angled nozzle 20x2 mm - angled               |
| EAN 4007841 007812  | Flat angled nozzle 20x2 mm, 100°                  |
| EAN 4007841 011864  | Reflector nozzle 35mm                             |
| EAN 4007841 093112  | Jointing plane including replacement blade        |
| EAN 4007841 034122  | Pressure roller 40mm - Teflon                     |
| EAN 4007841 0104166 | Sieve reflector nozzle 35 x 20 mm                 |