

Hot air tool - Professional Line

HG 2120 E carwrapper-set



EAN 4007841 011772
Article number 011772



CE



VDE

Function description

Experts in vehicle wrapping. Electronically controlled hot air tool HG 2120 E with 7.5 m cable and temperature scanner HL Scan. 2200 W, infinitely adjustable temperature from 80 – 630 °C, airflow rate adjustable from 150 – 500 l/min in 3 stages.

Technical specifications

Output	2200 W
Temperature	80 – 630 °C
Airflow rate	150 – 500 l/min
Motor, type	Brush motor
Function, life expectancy, motor	750 h
Temperature setting	Continuous
Temperature display	Thumbwheel with labelled settings
Heating element	Ceramic heating element
Loc function	No
Residual heat indicator	No
Function, hanger	Yes

Replaceable heating element	No
Restart protection	No
Thermal cut-out	Yes
Thermostat	No
Cord length	7.5 m
Dimensions (L x W x H)	253 x 87 x 200 mm
Mains power supply	220 – 230 V / 50 – 60 Hz
PU1, net weight	1,073 kg
Manufacturer's Warranty	1 year
PU1, EAN	4007841011772

Accessories

EAN 4007841 074210	ABS plastic welding rod
EAN 4007841 073411	PP plastic welding rod
EAN 4007841 071219	HDPE plastic welding rod
EAN 4007841 073114	PVC plastic welding rod
EAN 4007841 075569	12-piece hot-air accessory kit
EAN 4007841 009601	Flexible hot air tool stand with suction pad foot
EAN 4007841 014919	Temperature scanner HL Scan
EAN 4007841 009595	Flexible hot air tool stand with magnetic foot