

Hot air tool

HL 1820 S

EAN 4007841 033316

Article number 033316



CE



VDE

Function description

All-rounder on 3 levels. The three-stage HL 1820 S hot air tool with three temperature settings: 50, 400 and 600°C. A real all-rounder for de-icing, drying, shaping, heat shrinking, paint stripping, soft-soldering and much more.

Technical specifications

Output	1800 W
Temperature	50 – 600 °C
Airflow rate	100 – 500 l/min
Motor, type	Brush motor
Function, life expectancy, motor	600 h
Temperature setting	3-stage
Heating element	Micanite heating element
Loc function	No
Residual heat indicator	No
Function, hanger	Yes

Replaceable heating element	No
Restart protection	No
Thermal cut-out	Yes
Thermostat	No
Cord length	2.2 m
Dimensions (L x W x H)	253 x 85 x 200 mm
Mains power supply	220 – 230 V / 50 – 60 Hz
PU1, net weight	0,792 kg
Manufacturer's Warranty	3 years
PU1, EAN	4007841033316

Hot air tool

HL 1820 S



EAN 4007841 033316
Article number 033316

Accessories

EAN 4007841 009625	HL Light
EAN 4007841 034566	HL Tool Stand
EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 070113	Surface nozzle 50 mm
EAN 4007841 070410	Window nozzle 75 mm
EAN 4007841 070311	Window nozzle 50 mm
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 070519	Reflector nozzle
EAN 4007841 006655	Crimp connectors - Ø 0.5 - 1.5 mm
EAN 4007841 006662	Crimp connectors - Ø 0.1 - 6.0 mm
EAN 4007841 006648	Crimp connectors - Ø 1.5 - 2.5 mm
EAN 4007841 071417	Shrink tubing II - Ø 4,8 – 9,5 mm
EAN 4007841 071318	Shrink tubing I - Ø 1,6 – 4,8 mm
EAN 4007841 072766	Shrink tubing III - Ø 4,0 – 12,0 mm
EAN 4007841 075811	Shrink tubing kit
EAN 4007841 078218	Fine dust filter HL 1920 E - HG 2320 E