

42INOX
Klucze płasko-oczkowe wykonane ze stali nierdzewnej
DIN 3113 - UNI ISO 7738

- Główki o zredukowanych wymiarach
- Wysoka odporność na korozję.
- Znakomite właściwości mechaniczne.

	art.	 mm	L mm	A mm	Ø mm	S1 mm	S2 mm	 g
000420306	42INOX 6	6x6	95	15,2	10,1	3,4	5,2	18
000420307	42INOX 7	7x7	105	17,1	11,1	3,6	5,7	20
000420308	42INOX 8	8x8	116	19,0	12,3	3,9	3,3	22
000420309	42INOX 9	9x9	127	20,9	14,1	4,2	6,7	28
000420310	42INOX 10	10x10	137	22,8	15,1	4,5	4,0	33
000420311	42INOX 11	11x11	148	24,8	16,5	4,8	4,3	42
000420312	42INOX 12	12x12	158	26,9	18,2	5,1	4,6	56
000420313	42INOX 13	13x13	169	28,8	19,6	5,4	5,0	66
000420314	42INOX 14	14x14	180	30,8	21,0	5,7	5,2	75
000420315	42INOX 15	15x15	190	32,7	22,4	6,0	5,5	95
000420316	42INOX 16	16x16	201	34,6	23,8	6,3	9,7	120
000420317	42INOX 17	17x17	212	36,6	25,2	6,7	6,0	126
000420318	42INOX 18	18x18	222	38,5	26,7	7,0	10,8	135
000420319	42INOX 19	19x19	233	40,5	28,0	7,3	6,6	171
000420321	42INOX 21	21x21	254	44,5	30,7	7,9	12,4	180
000420322	42INOX 22	22x22	264	46,4	32,2	8,1	12,8	190
000420324	42INOX 24	24x24	285	50,3	34,9	8,5	13,5	230
000420327	42INOX 27	27x27	290	53,0	42,0	9,0	12,0	430
000420330	42INOX 30	30x30	320	59,0	46,0	10,0	13,0	530
000420332	42INOX 32	32x32	340	63,0	49,0	11,0	14,0	635
000420336	42INOX 36	36x36	360	70,0	55,0	16,0	21,0	960
000420338	42INOX 38	38x38	430	85,0	64,0	16,0	21,0	1300
000420341	42INOX 41	41x41	430	85,0	64,0	16,0	21,0	1300
000420343	42INOX 46	46x46	480	90,0	70,0	16,0	22,0	1760
000420345	42INOX 50	50x50	520	98,0	77,0	17,0	23,0	2000
000420347	42INOX 55	55x55	560	108,0	83,0	18,0	23,0	2500
000420350	42INOX 60	60x60	595	115,0	89,0	20,0	25,0	2900

