

96N
offset hexagon key wrenches, burnished

ISO 2936

	art.	mm	L mm	L1 mm	 g
000960409	96N 0,9	0,9	32	10	0,2
000960413	96N 1,3	1,3	44	12	0,6
000960415	96N 1,5	1,5	46	15	0,9
000960420	96N 2	2	51	17	1,7
000960425	96N 2,5	2,5	57	20	3
000960430	96N 3	3	64	22	4,9
000960435	96N 3,5	3,5	68	25	7,1
000960440	96N 4	4	72	28	9,9
000960445	96N 4,5	4,5	78	30	14
000960450	96N 5	5	83	32	17,7
000960460	96N 6	6	94	37	29
000960470	96N 7	7	99	40	41,5
000960480	96N 8	8	105	43	58,1
000960490	96N 9	9	111	46	77,4
000960500	96N 10	10	119	49	102
000960510	96N 11	11	126	52	127,7
000960520	96N 12	12	134	56	159
000960530	96N 13	13	142	62	204
000960540	96N 14	14	151	69	250
000960560	96N 16	16	165	72	366,8
000960570	96N 17	17	174	79	429
000960590	96N 19	19	194	88	598
000960592	96N 22	22	216	99	910
000960594	96N 24	24	242	111	1190

