






Notes:

1. pitch: 3.81mm poles: 2-24p
2. Rated voltage/current: UL 300V/8A
VDE 250V/12A
4. Insulation Resistance: 5000MΩ/DC1000V
5. Rated impulse voltage: AC2500V
6. Wire range: 28-16AWG 0.2-1.5mm²
7. Temp. Range: -40°C~+105°C
8. Undimensioned Tolerances:


Pitch range in mm		Nominal dimension range in mm						
to	over	to	over	to	over	to	over	
6	5	10	10	30	60	100	150	∅
±0.10	±0.15	±0.25	±0.2	±0.3	±0.5	±0.7	±1.0	±0.05/0.10



注: 2-6P带卡点, 7-24P, 不带卡点



5	15EDGKD spring	X000001310 (H)	XX	stainless steel	
4	15EDGKD PIN	1088B00010 (H)	XX	phosphor bronze	Snce plated
3	15EDGKD BUTTON	1088D0501A (H)	XX	POM	UL94HB
2	15EDGKD-3.81-COVER	1088C0YXXA (H)	1	PA66	UL94V-0

1		15EDGKD-3.81-HOUSING		1088A0YXXA(H)		1		PA66		UL94V-0	
ITEM		NAME OF PART		NO. OF PART		Q'TY		MATERIAL		NOTES	
DETACHED LISTS		 MM (INCH)		DFTD Zhong		DATE 05/31/07		 DEGSON  宁波高正电子有限公司 DEGSON ELECTRONICS CO., LTD			
		TOLERANCES EXCEPT AS NOTED		CHKD Alan		DATE 11/8/15					
				INFO		DATE					
				APPR Alex		DATE 1/18/13					
		MM .0 ± .00 ± .000 ±									
		ANGLES ± 1°		G.E :							
				FINISH :							
		THIRD ANGLE PROJECTION		SCALE :							
						NAME 15EDGKD-3.81-XXP-1Y-00A(H)					
						DRAWING NO. 15EDGKD-3.81-E01		SIZE A4		REV T8 11/13/13	
						/PART NO.					
						DO NOT SCALE DRAWING		SHEET 1		OF 1	