

Plastic cable markers - KMK 2

1005266

<https://www.phoenixcontact.com/pc/products/1005266>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Plastic cable markers, transparent, unlabeled, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, lettering field size: 29 x 8 mm



Your advantages

- Plastic cable markers for marking and bundling conductors and cables indoors
- Labeling service: Phoenix Contact can custom-label all insert labels for plastic cable markers according to your requirements
- The marked insert label is protected from dirt by the sealing cap

Plastic cable markers - KMK 2



1005266

<https://www.phoenixcontact.com/pc/products/1005266>

Commercial Data

Item number	1005266
Packing unit	100 pc
Minimum order quantity	100 pc
Product Key	BG231A
Catalog Page	Page 235 (C-3-2019)
GTIN	4017918012489
Weight per Piece (including packing)	1.07 g
Weight per Piece (excluding packing)	0.959 g
Customs tariff number	39269097
Country of origin	DE

Technical Data

Product properties

Product type	Marker carrier cable
Type	Mounting set

Dimensions

Width	8 mm
Height	8 mm
Length	29 mm

External dimensions

Outside diameter	6 mm ... 50 mm
------------------	----------------

Material specifications

Color	transparent
Material	Polyethylene
Components	free from silicone and halogen
Silicone-free	yes

Cable / line

Cable structure

External cable diameter	≥ 6 mm
-------------------------	--------

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

	VDMA 24364:2018-05
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h

Temperature resistance

Specification	Following ANSI/UL 969-2018:03
Test duration	240 h
Rating 80 °C (105 °C)	Test passed
Test duration	168 h

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Plastic cable markers - KMK 2



1005266

<https://www.phoenixcontact.com/pc/products/1005266>

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

Plastic cable markers - KMK 2

1005266

<https://www.phoenixcontact.com/pc/products/1005266>



Classifications

ECLASS

ECLASS-9.0	27400401
ECLASS-10.0.1	27400401
ECLASS-11.0	27281105

ETIM

ETIM 8.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Plastic cable markers - KMK 2

1005266

<https://www.phoenixcontact.com/pc/products/1005266>

Accessories

Insert strip

Insert strip - ESL 29X8 - 0808257

<https://www.phoenixcontact.com/pc/products/0808257>

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems: Laser printer, perforated, mounting type: insert, lettering field size: 29 x 8 mm, Number of individual labels: 174



Insert strip

Insert strip - ESL 29X8 YE - 0811930

<https://www.phoenixcontact.com/pc/products/0811930>

Insert strip, Sheet, yellow, unlabeled, can be labeled with: Office printing systems: Laser printer, mounting type: insert, lettering field size: 29 x 8 mm, Number of individual labels: 174



Plastic cable markers - KMK 2

1005266

<https://www.phoenixcontact.com/pc/products/1005266>

Snap-in markers

Snap-in markers - US-EMP (29X8) - 0829436

<https://www.phoenixcontact.com/pc/products/0829436>



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, lettering field size: 29 x 8 mm, Number of individual labels: 48

Snap-in markers

Snap-in markers - US-EMP (29X8) YE - 0829440

<https://www.phoenixcontact.com/pc/products/0829440>



Snap-in markers, Card, yellow, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: insert, lettering field size: 29 x 8 mm, Number of individual labels: 48

Plastic cable markers - KMK 2

1005266

<https://www.phoenixcontact.com/pc/products/1005266>

Insert label

Insert label - EMT (29X8)R - 0817277

<https://www.phoenixcontact.com/pc/products/0817277>



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter range: 10 ... 25 mm, lettering field size: 29 x 8 mm, Number of individual labels: 5400

Insert label

Insert label - EMT (29X8)R YE - 0817280

<https://www.phoenixcontact.com/pc/products/0817280>



Insert label, Roll, yellow, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter range: 10 ... 25 mm, lettering field size: 29 x 8 mm, Number of individual labels: 5400

Plastic cable markers - KMK 2



1005266

<https://www.phoenixcontact.com/pc/products/1005266>

Marker for terminal blocks

Marker for terminal blocks - TMT (EX8)R - 0803066

<https://www.phoenixcontact.com/pc/products/0803066>



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMaster 300/600, THERMOMARK X1.2, mounting type: snapped, snap into flat marker groove, for terminal block width: 50000 mm, lettering field size: 8 x 50,000 mm, Number of individual labels: 1

Insert label

Insert label - MM-EMT (EX8)R C1 WH/BK - 0803965

<https://www.phoenixcontact.com/pc/products/0803965>



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped, lettering field size: continuous x 6 mm

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com