

1201E

Evox screwdrivers for slotted head screws, chrome-plated, black tips


ISO 2380

Features:

- Bi-material handle for maximum force transmission with minimum effort and optimal comfort.
- The ergonomic design fits the palm of the hand perfectly.
- The style and size of the tip are printed on the round cap for quick identification.
- Beta's tried and tested blades ensure unique elasticity, hardness and wear resistance, for top-end professional tools.
- Chrome-plating free tip for perfect screw coupling, protected from oxidation with phosphate-coating treatment
- The brand-new hole on the handle allows the screwdriver to hang for easy storage

The evolution of the screwdriver!

	art.	SxAXL mm	L1 mm	Ø mm	
012011003	1201E 2,5X50	0,4x2,5x50	146	2,5	35,0
012011006	1201E 2,5X75	0,4x2,5x75	166	2,5	35,5
012011009	1201E 3X75	0,5x3x75	171	3,0	37,4
012011012	1201E 3X100	0,5x3x100	196	3,0	40,0
012011018	1201E 3,5X75	0,6x3,5x75	171	3,5	41,1
012011021	1201E 3,5X100	0,6x3,5x100	196	3,5	41,2
012011030	1201E 4X100	0,8x4x100	196	4,0	44,6
012011033	1201E 4X125	0,8x4x125	221	4,0	46,6
012011036	1201E 4X150	0,8x4x150	246	4,0	50,3
012011039	1201E 5,5X100	1,0x5,5x100	209	5,0	68,6
012011040	1201E 5,5X125	1,0x5,5x125	234	5,0	70,5
012011042	1201E 5,5X150	1,0x5,5x150	259	5,0	75,8
012011048	1201E 6,5X100	1,2x6,5x100	220	6,0	95,8
012011050	1201E	1,2x6,5x125	234	6,0	99
012011051	1201E 6,5X150	1,2x6,5x150	270	6,0	104,8
012011057	1201E 8X150	1,2x8x150	282	8,0	159
012011060	1201E 8X200	1,2x8x200	332	8,0	209,8
012011066	1201E 10X200	1,6x10x200	332	9,5	220,6

