

**1662AN**
**adjustable stylus dial indicator, reading to 0.01 mm**
**DIN 2270**

- Centesimal reading
  - Rotating dial
  - 2 mm dia. carbide probe
  - High-precision movement mounted on rubies
  - Shank  $\varnothing$  8 mm
- C= Comparison range  
C= Dial field

|  | art.   | C<br>mm | B<br>mm | D<br>mm | G<br>mm | <br>g |
|----------------------------------------------------------------------------------|--------|---------|---------|---------|---------|----------------------------------------------------------------------------------------|
| <b>016620200</b>                                                                 | 1662AN | 0÷0,8   | 12      | 32      | 0,01    | 50                                                                                     |

