

1666A
flanged precision squares made from stainless steel ground and lapped
DIN 875/0

	art.	L mm	L1 mm	B mm	C mm	H mm	S mm	g
016660110	1666A 100	100	70	23,4	5,0	20,0	5,5	185
016660115	1666A 150	150	100	23,4	6,0	24,5	5,5	330
016660120	1666A 200	200	130	27,5	6,0	28,5	6,0	560
016660125	1666A 250	250	170	32	7,0	36,0	8,0	1050
016660130	1666A 300	300	200	38	8,0	39,0	8,0	1500

