

1680 trammels, hardened steel body and tips

- Mm-scale
- Interchangeable tips
- Fine tip adjustment to 0.02 mm
- Fine tip adjustment to 0.02 mm

	art.	L mm	A Max mm	G mm	HxS mm	g
016800050	1680 500	660	500	0,05	30x6	1,2

