

1680B
outside callipers

	art.	L mm	A Max mm	L1 mm	g
016800215	1680B 150	150	155	200	135
016800220	1680B 200	200	190	260	185
016800225	1680B 250	250	235	310	225
016800230	1680B 300	300	280	345	260

