

666HS
**Click-type torque wrenches with reversible ratchets for right-hand tightening
torque accuracy: $\pm 3\%$ H-SAFE**
ISO 6789

LC system,
two-ball retaining system.
Socket is only released
through button

with H-SAFE tethered system

	art.	Nm	Kgfm	lbf.ft	■	D mm	A mm	L mm	LC system	g
006664005	666HS/5	10÷50	1÷5	7÷37	3/8	30	33	312		660
006664010	666HS/10	20÷100	2÷10	15÷75	3/8	30	33	381		730
006664021	666HS/20LC	40÷200	4÷20	30÷150	1/2	40	43	470	•	1010
006664031	666HS/30LC	60÷300	6÷30	50÷220	1/2	40	43	598	•	1380

