

89MQ
single ring wrenches

EN 60900

	art.	mm	L mm	A mm	D mm	S mm	
000890106	89MQ 6	6	150	12	15	5,8	46
000890107	89MQ 7	7	155	13	15	6,2	60
000890108	89MQ 8	8	155	15	15	7	60
000890109	89MQ 9	9	160	16	15	8	60
000890110	89MQ 10	10	170	19	17	9,5	75
000890111	89MQ 11	11	180	20,3	17,5	10	74
000890112	89MQ 12	12	190	21,8	21	10	132
000890113	89MQ 13	13	195	23	21	10,5	106
000890114	89MQ 14	14	200	24,6	21,2	11	168
000890115	89MQ 15	15	210	25,5	21	10,8	161
000890116	89MQ 16	16	216	27	21	12	202
000890117	89MQ 17	17	218	30	22	13	209
000890118	89MQ 18	18	236	30	22	11	260
000890119	89MQ 19	19	240	31,5	25	12	307
000890121	89MQ 21	21	250	34	25	12	310
000890122	89MQ 22	22	255	35,5	28	15	350
000890124	89MQ 24	24	280	39	29	16	425
000890127	89MQ 27	27	300	45	29	17	540
000890130	89MQ 30	30	320	46	29	18	580
000890132	89MQ 32	32	340	48	29	19	590

