

5935ET/1MB
Assortment of 96 tools for electrotechnical maintenance in EVA foam trays

Electrotechnical maintenance

		art.
	059351332	5935ET/1MB



MB65



MB64



MB63



MB65



MB64



MB63

- n. 1 **1052**: self - locking pliers 240 mm
- n. 1 **1370**: engineer's hammer 500 g
- n. 1 **1390**: soft face hammer Ø 35 mm
- n. 1 **1719BMA...Q**: second-cut square files 200 mm
- n. 1 **1719BMA...P**: second-cut flat files 200 mm
- n. 1 **1719BMA...T**: second-cut triangular files 200 mm
- n. 1 **1719BMA...M**: second-cut half-round files 200 mm
- n. 1 **1719BMA...R**: second-cut round files 200 mm
- n. 1 **35**: flat chisels, ribbed type 200 mm
- n. 1 **1032**: circlip pliers straight, internal ☉ 180 mm
- n. 1 **1034**: circlip pliers bent, internal ☉ 170 mm
- n. 1 **1036**: circlip pliers straight, external ● 175 mm
- n. 1 **1038**: circlip pliers bent, external ● 175 mm
- n. 1 **1084BM**: Heavy-duty diagonal cutting nippers □ 160 mm
- n. 1 **1150BM**: half-round needle nose pliers = 180 mm
- n. 1 **1166BM**: Extra-long needle nose pliers ● 160 mm
- n. 9 **96BPC/SC9**: ball head offset hexagon key wrenches ○
- n. 1 **1250**: screwholding screwdriver for slotted head screws ●
- n. 1 **1251**: screwholding screwdriver for cross head Phillips® screws ⊕
- n. 1 **1253**: mains testing screwdriver ●
- n. 6 **943MQ**: hexagon nut spinners with handles ○ 5,5-6-7-8-10-13 mm
- n. 4 **1272MQ**: screwdrivers for cross head Phillips® screws, 1000V ⊕ PH0x60-PH1x80-PH2x100-PH3x150 mm
- n. 6 **1274MQ**: screwdrivers for headless slotted screws, 1000V ● 2,5x75-3x100-4x100-5,5x125-6x150-8x175 mm
- n. 31 **860MIX/A31**: bits with magnetic quick release bit holder in plastic case ● ○ ⊕ ⊕ ⊕ ⊕
- n. 1 **850MQ**: magnetic bit holder, insulated ®
- n. 8 **55**: double open end wrenches 6x7-8x9-10x11-12x13-14x15 16x17-18x19-20x22 mm
- n. 1 **1048MQ**: slip joint pliers, boxed joint 250 mm
- n. 1 **1082MQ**: diagonal cutting nippers 1000V □ 140 mm