

TOOL SET BOSS

► 6500 tool case BOSS 113 pcs

► 6500R tool case BOSS with wheels 113 pcs

The mobile workshop in a case

The rigid and robust roller case for heavy loads. With a double aluminium frame and the break-resistant X-ABS case shells, the case can carry loads of up to 40 kg and is also airworthy. The 4-fold telescopic pull-out is powder-coated and has an ergonomic handle that is form-fitting with the case handle.

The wide wheelbase and the rubberised and mounted rollers allow the PROTECTION XL to also master uneven paths. The ratchet hinges with case lid lock come as standard with our tool cases.

Art.-No.	Content
6515	tool case PROTECTION XL BOSS 90 empty pockets
1-151	plastic adjusting screwdriver slot blade 3 x 0.5 x 40 mm
1-153	plastic adjusting screwdriver slot blade 2 x 0.7 x 130 mm
1-155	plastic adjusting screwdriver slot blade 3.5 x 0.7 x 130 mm
1-909	engineer mirror with extension Ø 23 mm
2-126	ESD desoldering lever slotted at one ends
2-127	ESD tin knife pointed sharp blade
2-128	ESD tin scraper sharp chisel form
2-132	spring puller 175 mm
2-155	claw-type gripper with 3 hardened wire claws
2-161	scriber, magnetic lifter with telescopic slide-out
2-166	glass fibre contact cleaner brush Ø 4mm
2-265-1	test prod red blade 1 mm
2-265-2	test prod black blade 1 mm
2-296	hand magnifier 3 x magnification LED light
2-601	IC-tweezers 125 mm
2-620	PLCC-extractor
2-656	LED flashlight 143 x 19 mm
3-0856	crimping pliers wire stripper
3-132-16	side cutters 130 mm
3-235-16	telephone pliers 160 mm with serration jaws length 55 mm
3-601-15	ESD side cutters CLASSICline semi flush 115 mm
3-603-15	ESD side cutters CLASSICline semi flush 115 mm
3-606-15	ESD side cutters CLASSICline flush 120 mm
3-632-15	ESD flat nose pliers CLASSICline not serrated jaws 120 mm
3-633-15	ESD snipe nose pliers CLASSICline not serrated jaws 120 mm
3-634-15	ESD snipe nose pliers CLASSICline not serrated jaws 120 mm
3-732-16	combinations pliers 165 mm with serration
3-815-16	wire stripper with adjusting screw and opening spring
3-871-6	pressing pliers 155 mm for wire 0.25-2.5 mm ²
4-301	Liliput screwdriver slot blade 2,0 x 0.65 x 40 mm
4-343 VDE	VDE voltage tester slot blade 3.0 x 0.7 x 60 mm
4-351	offset screwdriver slot blade 4.5 x 0.65 x 100 mm

Art.-No.	Content
4-392	watchmaker screwdriver magazin 6 pcs (1.5 - 2.0 - 2.5 - 3.0 - PH0 + handle)
4-504	screwdriver EUROline-Power slot blade 5.5 x 1.0 x 100 mm
4-523	screwdriver EUROline-Power slot blade 4.0 x 0.8 x 100 mm
4-543	screwdriver EUROline Power cross-recess PZ1
4-603	ESD screwdriver slot blade 1.5 x 0.25 x 40 mm
4-605	ESD screwdriver slot blade 2.0 x 0.40 x 40 mm
4-606	ESD screwdriver slot blade 2.5 x 0.4 x 50 mm
4-607	ESD screwdriver slot blade 3.0 x 0.5 x 50 mm
4-608	ESD screwdriver slot blade 3.5 x 0.6 x 60 mm
4-621	ESD screwdriver cross-recess PH000
4-622	ESD screwdriver cross-recess PH00
4-623	ESD screwdriver cross-recess PH0
4-624	ESD screwdriver cross-recess PH1
5-006	component tweezers 145 mm jaws insulated
5-049	SMD tweezers 110 mm form 4 stainless steel
5-107	anatomical tweezers 150 mm form 22b
5-107-6	tweezers 150 mm form 22b teething,insulated
5-115	thermal tweezers 165 mm form R30 cross tweezers
5-117	anatomical tweezers 145 mm form 40 serrated
5-161	clamping scissors with teething jaws
5-181	wire scraper tweezers 125 mm
5-191	ESD plastic tweezers 120 mm form 2a tips 2 mm wide
5-194	ESD plastic tweezers 120 mm form 6
5-210	needle files set 6 pcs (flat, round, blunt, pointed, 3-edge, 4-edge)
5-301	scissors with teething
5-305	scissors 140 mm
5-501	cable knife (open 200 mm)
5-515	cutter knife 140 mm
4-775	socket wrenches handle plastic spring-haft
6-201	socket wrench 4.0 mm without handle
6-202	socket wrench 5.5 mm without handle
6-203	socket wrench 6.0 mm without handle

Art.-No.	Content
6-204	socket wrench 7.0 mm without handle
6-205	socket wrench 8.0 mm without handle
6-206	socket wrench 9.0 mm without handle
6-207	socket wrench 10.0 mm without handle
6-611	ESD socket wrench 1.5 mm
6-631	ESD wrench key 0.7 mm
6-632	ESD wrench key 0.9 mm
6-633	ESD wrench key 1.3 mm
6-634	ESD wrench key 1.5 mm
6-635	ESD wrench key 2.0 mm
6-658	ESD torx screwdriver T3
6-659	ESD torx screwdriver T4
6-661	ESD torx screwdriver T5
6-662	ESD torx screwdriver T6
6-663 L	ESD torx screwdriver T7
6-664 L	ESD torx screwdriver T8
6-750-3	double open-ended wrench 3 x 3.5 mm
6-750-4	double open-ended wrench 4 x 4.5 mm
6-750-5	double open-ended wrench 5 x 5.5 mm
6-750-6	double open-ended wrench 6 x 6.5 mm
6-750-7	double open-ended wrench 7 x 8 mm
6-750-9	double open-ended wrench 9 x 10 mm
6-771	adjustable wrench 0 - 13 mm
6-820	wrench key set 8 pcs (1.5 - 2.0 - 2.5 - 3.0 - 4.0 - 5.0 - 5.5 - 6.0)

Art.-No.	Content
6-984 L	screwdriver EUROLiNE-Power TORX T9 with hole
6-985 L	screwdriver EUROLiNE-Power TORX T10 with hole
6-986 L	screwdriver EUROLiNE-Power TORX T15 with hole
7-425	dust brush bristles width 25 mm
7-506	tape measure 2 m
7-508	steel tape measure 30 cm
7-511	digital caliper DIN862 precision 150 mm
7-616	PUK saw in case



Inner dimension: 470 x 360 x 210 mm



with tools, portable: 10400 g
with tools, rollable: 11900 g



113 tools



6500 R BOSS with tools, rollable

6515 R BOSS without tools, rollable

6500 BOSS with tools, portable

6515 BOSS without tools, portable