

TOOL SET TELECOM

► 6600 tool case TELECOM 124 pcs

► 6600 R tool case TELECOM with wheels 12 pcs

The case with special tools and test equipment for the installation and maintenance of complex telecommunications systems as well as for working with VDE-insulated tools.

The rigid and robust roller case for heavy loads. With a double aluminium frame and the break-resistant X-ABS case shells, the case can carry loads of up to 40 kg and is also airworthy. The 4-fold telescopic pull-out is powder-coated and has an

ergonomic handle that complements the case handle in a form-fit manner. The wide wheelbase and the rubberised and mounted rollers allow the PROTECTION XL to also master uneven paths. The ratchet hinges with case lid lock come as standard with our tool cases.

Art.-No.	Content
6615	tool case PROTECTION XL 42 empty pockets
13-906 VDE	VDE side cutters 160 mm
13-915 VDE	VDE telephone pliers 160 mm serrated jaws straight with wire cutters
13-927 VDE	VDE flat nose pliers 160 mm with serration
13-936 VDE	VDE combination pliers 160 mm with serration
14-651 VDE	VDE screwdriver slot blade 2.5 x 75 mm
14-652 VDE	VDE screwdriver slot blade 3.5 x 100 mm
14-653 VDE	VDE screwdriver slot blade 4.0 x 100 mm
14-654 VDE	VDE screwdriver slot blade 5.5 x 125 mm
14-681 VDE	VDE screwdriver cross-recess PH0 Ø 3.0 mm
14-682 VDE	VDE screwdriver cross-recess PH1 Ø 4.5 mm
14-683 VDE	VDE screwdriver cross-recess PH2 Ø 6.0 mm
16-299 VDE	VDE socket wrench 4.0 mm
16-301 VDE	VDE socket wrench 5.0 mm
16-302 VDE	VDE socket wrench 5.5 mm
2-265-1	test prod red blade 1 mm
2-265-2	test prod black blade 1 mm
2-275	magnifying mirror Ø 21 mm 180 mm
2-601	IC-tweezers 125 mm
2-656	PLCC-extractor
2-620	LED flashlight 143 x 19 mm
2-701	LSA-Plus insertion tool
3-0605	combination crimping pliers
3-573	water pump pliers 180mm with push-button

Art.-No.	Content
3-601-15	ESD side cutters CLASSICline semi flush 115 mm
4-360-E03	watchmakers screwdriver set 6pcs (slot 0.6 - 1.0 - 1.5 - 2.0 - 2.5 - 3.0)
5-107	anatomical tweezers 150 mm form 22b
5-117	anatomical tweezers 145 mm form 40 serrated
5-240	warding files set 6 pcs (flat, round, blunt, pointed, 3-edge, 4-edge)
5-505	stripping knife Ø 4 - 28 mm with hook blade
5-535	coax cable stripper Ø 4.8 - 7.5 mm
6-320	socket wrench set 36 pcs with ratchet+extension
6-500	double open-ended wrench set 8 pcs (6 x 7 - 8 x 9 - 10 x 11 - 12 x 13 - 14 x 15 - 16 x 17 - 18 x 19 - 20 - 22)
6-600	combination wrench set 12 pcs (6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 - 17 - 19 - 22)
6-950	ballpoint wrench key set 9 pcs (1.5 - 2.0 - 2.5 - 3.0 - 4.0 - 5.0 - 6.0 - 8.0 - 10.0)
6-995	TORX wrench key set with hole 8 pcs (T9 - T10 - T15 - T20 - T25 - T27 - T30 - T40)
7-114	engineer hammer to DIN 1041, 200 g
7-425	dust brush bristles width 25 mm
7-429	insulating tape 25 mm wide, 25 m (12 mm core)
7-506	tape measure 2 m
7-616	PUK saw in case
8-376	gas soldering iron Independent 75
8-390	desoldering suction pump PRAKTIK 20 mm diameter RD-7376
9-316	ESD chip-container 57 x 36 x 17 mm





Inner dimension: 470 x 360 x 210 mm



with tools, portabel: 11900 g
with tools, rollable: 13500 g



124 tools



6600 R tool case TELECOM with tools, rollable
6615 R tool case TELECOM without tools, rollable
6600 tool case TELECOM with tools,
6615 tool case TELECOM without tools

