




Note:



L(Length) Unit:mm	T(Tolerance) Unit:mm	Part number	Color
1000	20	SN319-3/10/1BK	BLK
1800	50	SN319-3/10/1.8BK	BLK
3000	50	SN319-3/10/3BK	BLK
5000	50	SN319-3/10/5BK	BLK
1000	20	SN319-3/10/1WH	WHT
1800	50	SN319-3/10/1.8WH	WHT
3000	50	SN319-3/10/3WH	WHT
5000	50	SN319-3/10/5WH	WHT
1000	20	SN319-3/10/1GY	GRY
1800	50	SN319-3/10/1.8GY	GRY
3000	50	SN319-3/10/3GY	GRY
5000	50	SN319-3/10/5GY	GRY



NOTE :

1. PLUG : LT-319 ITALY TYPE
2. CONNECTOR : LT-501 IEC 60320 C13
3. Strain relief : NA
4. CORD : H05VV-F 3G1.0mm² BK 1m 1.8m 3m 5m/WHT 1m 1.8m 3m 5m/GRY 1m 1.8m 3m 5m
5. APPROVALS : IMQ
6. CUSTOMER : TME
7. Supplier for flexible cord : RHYTHM、LIAN DUNG、I-SHENG
8. P/N : Above Note Chart

修改履歷

6		
5		
4		
3		
2		
1	新增	22/04/01
REV.	DESCRIPTION	DATE

DRAWER	Aaron	DATE	22/04/01	TITLE	LT-319+501
APPROVE		REV.	1	Dr.No.	1110403
		TOL.	±5mm		
		ALL DIMENSIONS IN mm			

※Customer drawing number : NA



LIAN DUNG
ELECTRIC WIRE MATERIAL CO.,LTD.
聯東電線材料股份有限公司