




Note:

L(Length) Unit:mm	T(Tolerance) Unit:mm	Part number	Color
1000	20	WN114-3/07/1BK	BLK
1800	50	WN114-3/07/1.8BK	BLK
1000	20	WN114-3/07/1WH	WHT
1800	50	WN114-3/07/1.8WH	WHT
1000	20	WN114-3/07/1GY	GRY
1800	50	WN114-3/07/1.8GY	GRY

NOTE :


1. PLUG : LT-602 EUROPEAN TYPE
2. CONNECTOR : LT-511R IEC 60320 C13
3. Strain relief : NA
4. CORD : H05VV-F 3G0.75mm² BK 1m 1.8m/WHT 1m 1.8m/GRY 1m 1.8m
5. APPROVALS : PSE EAC SEMKO OVE SEV CEBEC VDE KC KEMA SAA VDE FIMKO IRAM IMQ DEMKO CCC
6. CUSTOMER : TME
7. Supplier for flexible cord : RHYTHM、LIAN DUNG、I-SHENG
8. P/N : Above Note Chart

※Customer drawing number : NA

修改履歷

6		
5		
4		
3		
2		
1	新增	22/04/01
REV.	DESCRIPTION	DATE

DRAWER	Aaron	DATE	22/04/01	TITLE	LT-602+511R
APPROVE		REV.	1	Dr.No.	1110404
		TOL.	±5mm		
		ALL DIMENSIONS IN mm			



比例



LIAN DUNG
ELECTRIC WIRE MATERIAL CO.,LTD.
聯東電線材料股份有限公司