




Click [here](#) for the 3D model.

Dimensions	
L	42mm +/-1mm
H	37mm +/-1mm
T	28mm +/-1mm
S	37.5mm +/-0.4mm
S1	10.2mm +/-0.4mm
LL	6mm -2mm
F	1.2mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Box
Packaging Quantity	36

General Information	
Series	C4AK
Dielectric	Metallized Polypropylene
Style	Radial
Features	DC Filtering
RoHS	Yes
Lead	4 Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Component Weight	74.7 g
Miscellaneous	Rth = 18 C/W.

Specifications	
Capacitance	14 uF
Capacitance Tolerance	5%
Voltage DC	900 VDC
Temperature Range	-55/+135°C
Insulation Resistance	2.14 GOhms
Max dV/dt	20 V/us
Resistance	5.94 mOhms (10kHz 70C)
Ripple Current	14.4 Amps Irms (10kHz 95C), 280 Amps Ipk
Inductance	10 nH