

FG26C0G2A104JRT06



Application

Commercial Grade

Series

FG26

Dimensions

L	
W	6mm Max.
T	3.5mm Max.
F	5mm +/-1mm
d	0.5mm +0.1,-0.03mm

Temperature Characteristic

-55 to 125°C 0+/-30ppm/°C

Rated Voltage

100Vdc

Capacitance

100nF

Capacitance Tolerance

+/-5%

Q Factor

1000 Min

Insulation Resistance

5000Mohm Min.

AEC-Q200

No

