



Technical sheet

No.

11FA11A

Issue

V01.0

Product family: Cable-ties - Nylon accessories
Item code: B0905, B0906
Description: ACCESSORIES FOR NYLON CABLE-TIES · ONE WAY CABLE TIE MOUNTS

Image



Specifications

MATERIAL: polyamide (PA 6.6)
COLOR: natural
INSULATION SELF-EXTINGUISHING: UL 94 V2
OPERATING TEMPERATURE: from -40 °C to +85 °C
MINIMUM INSTALLATION TEMPERATURE: -10 °C
CHEMICAL RESISTANCE: good resistance to bases, oils, grease, chloride solvents. Limited resistance to acids. Not resistant to phenols.

Code	For cable ties with max width (mm)	Dimensions (mm)	Height (mm)	Fixing hole Ø (mm)	Fixing screw Ø (mm)	
B0905	3,6	15,2 x 9,4	6,8	3,3	3	100/3000
B0906	9	22 x 16,2	10,8	5,2	5	100/1000

**HALOGEN
FREE**