



Technical sheet

No.

11FA02A

Issue

V01.0

Product family: Cable-ties - Nylon cable-ties
Item code: B1025V0, B1536V0, B2036V0, B2048V0, B3048V0, B3848V0, B3876V0
Description: NYLON CABLE-TIES · SELF-EXTINGUISHING UL94-V0

Image



Specifications

MATERIAL: polyamide (PA 6.6)
COLOR: white
INSULATION SELF-EXTINGUISHING: UL 94 V0
OPERATING TEMPERATURE: from -40 °C to +85 °C
MINIMUM INSTALLATION TEMPERATURE: -10 °C
CHEMICAL RESISTANCE: good resistance to bases, oils, grease, chloride solvents. Limited resistance to acids. Not resistant to phenols.
ACCORDING TO STD.: EN 62275:2015-02
CLASSIFICATION: type 1 (EN)
ASSEMBLY: open the package just before use

Code	Width (mm)	Length (mm)	Max bundle Ø (mm)	Min bundle Ø (mm)	Tensile minimum resistance (N)	
B1025V0	2,5	100	20,5	3	80	100/5000
B1536V0	3,6	150	36	3,5	180	100/2500
B2036V0	3,6	200	52,5	3,5	180	100/2000
B2048V0	4,8	200	49,5	3,5	230	100/1500
B3048V0	4,8	300	81	3,5	230	100/1000
B3848V0	4,8	370	106,7	3,5	230	100/2500
B3876V0	7,6	370	106,7	8,5	540	100/1000



**HALOGEN
FREE**

V0