



Technical sheet

No. **11FA06A**

Issue **V01.1**

Product family: Cable-ties - Nylon cable-ties
Item code: BH1125, BH2048, BH3076
Description: NYLON CABLE-TIES · WITH MOUNTING HOLE

Image



Specifications

MATERIAL: polyamide (PA 6.6)
COLOR: natural
INSULATION SELF-EXTINGUISHING: UL 94 V2
OPERATING TEMPERATURE: from -40 °C to +85 °C
MINIMUM INSTALLATION TEMPERATURE: -10 °C
CHEMICAL RESISTANCE: good resistance to bases, oils, grease, chloride solvents. Limited resistance to acids. Not resistant to phenols.
ACCORDING TO STD.: EN 62275:2015-02
CLASSIFICATION: type 1 (EN), type 21 (UL)
ASSEMBLY: open the package just before use

Code	Width (mm)	Length (mm)	Fixing hole Ø (mm)	Max bundle Ø (mm)	Min bundle Ø (mm)	Tensile minimum resistance (N)	
BH1125	2,5	110	3	19	3	80	100/3000
BH2048*	4,8	200	4,8	49,8	3	230	100/1000
BH3076*	7,6	305	6,1	78,7	8	550	100/1000



* file n° E 223175

**HALOGEN
FREE**